

DATA SHEET

GENERAL PURPOSE CHIP RESISTORS

RC0603

5%, 1%, 0.5%, 0.1%

RoHS compliant



YAGEO Phi(comp



SCOPE

This specification describes RC0603 series chip resistors with lead-free terminations made by thick film process.

APPLICATIONS

• All general purpose application

FEATURES

- RoHS compliant
 - Products with lead free terminations meet RoHS requirements
 - Pb-glass contained in electrodes, resistor element and glass are exempted by RoHS
- Reducing environmentally hazardous wastes
- High component and equipment reliability
- Saving of PCB space
- None forbidden-materials used in products/production
- Halogen Free Epoxy

ORDERING INFORMATION - GLOBAL PART NUMBER & 12NC

Both part numbers are identified by the series, size, tolerance, packing type, temperature coefficient, taping reel and resistance value.

YAGEO BRAND ordering code

GLOBAL PART NUMBER (PREFERRED)

X R - XX XXXX L (1) (2) (3) (4)

(I) TOLERANCE

 $D = \pm 0.5\%$

 $B = \pm 0.1\%$

 $D = \pm 0.5\%$

 $F = \pm 1\%$

 $J = \pm 5\%$ (for Jumper ordering, use code of J)

(2) PACKAGING TYPE

R = Paper / PE taping reel

(3) TEMPERATURE COEFFICIENT OF RESISTANCE

- = Base on spec

(4) TAPING REEL

07 = 7 inch dia, Reel

13 = 13 inch dia, Reel

(5) RESISTANCE VALUE

There are 2~4 digits indicated the resistor value. Letter R/K/M is decimal point, no need to mention the last zero after R/K/M, e.g.1K2, not 1K20.

Detailed resistance rules show in table of "Resistance rule of global part number".

(6) DEFAULTCODE

Letter L is the system default code for ordering only. (Note)

Resistance rule of global part number

Resistance code rul	le Example
0R	0R = Jumper
XRXX (1 to 9.76 Ω)	IR = I Ω IR5 = I.5 Ω 9R76 = 9.76 Ω
XXRX (10 to 97.6 Ω)	10R = 10 Ω 97R6 = 97.6 Ω
XXXR (100 to 976 Ω)	100R = 100 Ω
XKXX (1 to 9.76 KΩ)	IK = 1,000 Ω 9K76 = 9760 Ω
XMXX (1 to 9,76 M Ω)	$IM = 1,000,000 \Omega$ $9M76 = 9,760,000 \Omega$

ORDERING EXAMPLE

The ordering code of a RC0603 chip resistor, value 56 X with ±1% tolerance, supplied in 7-inch tape reel is: RC0603FR-0756RL.

NOTE

- I. All our RSMD products meet RoHS compliant. "LFP" of the internal 2D reel label mentions "Lead Free Process"
- 2. On customized label, "LFP" or specific symbol printed and the optional "L" at the end of GLOBAL PART NUMBER / 12NC can be added (both are on customer request)



0603 (RoHS Compliant)

PHYCOMP BRAND ordering codes

Both GLOBAL PART NUMBER (preferred) and I2NC (traditional) codes are acceptable to order Phycomp brand products.

GLOBAL PART NUMBER (PREFERRED)

For detailed information of GLOBAL PART NUMBER and ordering example, please refer to page 2.

12NC CODE

2322 / 2350	XXX	X	<u>x</u> xxx	L
(1)	(2	2)	(3)	(4)

TYPE/	START	TOL.	RESISTANCE	PAPER / PE TAPE ON REEL (units)		
0603	IN ⁽¹⁾	(%)	RANGE	5,000	10,000/not preferred	20,000
RC21	2322	±5%	I to $10M\Omega$	702 60xxx	702 70xxx	702 81xxx
RC22	2322	±1%	I to I0 $M\Omega$	704 6xxx	704 7xxx	704 8xxxx
HRC21	2350	±5%	II to 22 M Ω	522 I0xxx	-	-
Jumper	2322	_	0 Ω	702 96001	702 97001	702 92002

- (1) The resistors have a 12-digit ordering code starting with 2322 / 2350.
- (2) The subsequent 4 or 5 digits indicate the resistor tolerance and packaging.
- (3) The remaining 4 or 3 digits represent the resistance value with the last digit indicating the multiplier as shown in the table of "Last digit of I2NC".
- (4) "L" is optional symbol (Note).

ORDERING EXAMPLE

The ordering code of a RC22 resistor, value $56 \times$ with $\pm 1\%$ tolerance, supplied in tape of 5,000 units per reel is: 232270465609(L) or RC0603FR-0756R(L).

Last digit of I2NC	
Resistance decade (3)	Last digit
0.01 to 0.0976 X	0
0.1 to 0.976 $ imes$	7
I to 9.76 X	8
10 to 97.6 $ imes$	9
100 to 976 X	1
I to 9.76 KX	2
10 to 97.6 KX	3
100 to 976 KX	4
I to 9.76 M $ imes$	5
10 to 97.6 MX	6

Example:	0.02 X	=	0200 or 200
	0.3 X	=	3007 or 307
	ΙX	=	1008 or 108
	33 KX	=	3303 or 333
	I0 MX	=	1006 or 106

NOTE

- I. All our RSMD products are RoHS compliant. "LFP" of the internal 2D reel label mentions "Lead Free Process"
- 2. On customized label, "LFP" or specific symbol printed and the optional "L" at the end of GLOBAL PART NUMBER / I2NC can be added (both are on customer request)



MARKING

RC0603



E-24 series: 3 digits

First two digits for significant figure and 3rd digit for number of zeros





E-96 series: 3 digits for 0603 ±1% EIA-96 marking method

For 0603 ±1% E-24 series, one short bar under marking letter

For further marking information, please see special data sheet "Chip resistors marking".


CONSTRUCTION

The resistor is constructed on top of a high-grade ceramic body. Internal metal electrodes are added on each end to make the contacts to the thick film resistive element. The composition of the resistive element is a noble metal imbedded into a glass and covered by a second glass to prevent environment influences. The resistor is laser trimmed to the rated resistance value. The resistor is covered with a protective epoxy coat, finally the two external terminations (matte tin on Nibarrier) are added. See fig.4

DIMENSIONS

Table I	
TYPE	RC0603
L (mm)	1.60 ±0.10
W (mm)	0.80 ±0.10
H (mm)	0.45 ±0.10
I _I (mm)	0.25 ±0.15
I ₂ (mm)	0.25 ±0.15

OUTLINES







Chip Resistor Surface Mount

RC SERIES 0603 (RoHS Compliant)

ELECTRICAL CHARACTERISTICS

 Га	h	le	2
ıa	0		_

CHARACTERISTICS	R	C0603 1/10 W
Operating Temperature Range	- 55	°C to +155 °C
Maximum Working Voltage		75 V
Maximum Overload Voltage		150 V
Dielectric Withstanding Voltage		100 V
	5% (E24)	I Ω to 22 M Ω
Resistance Range	1% (E24/E96)	I Ω to I0 $M\Omega$
Resistance Range	0.i%, 0.5% (E24/E96)	10Ω to $1M\Omega$
	Zero Ohm Ju	umper $< 0.05 \Omega$
	$1 \Omega \le R \le 10\Omega$	±200 ppm/°C
Temperature Coefficient	$10 \text{ M}\Omega < R \le 22 \text{ M}\Omega$	±200 ppm/°C
	$10 \Omega < R \le 10 M\Omega$	±100 ppm/°C
Jumper Criteria	Rated Current	1.0 A
Juniper Criteria	Maximum Current	2.0 A

FOOTPRINT AND SOLDERING **PROFILES**

For recommended footprint and soldering profiles, please see the special data sheet "Chip resistors mounting".

PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

PRODUCT TYPE	PACKING STYLE	REEL DIMENSION	QUANTITY PER REEL
RC0603	Paper Taping Reel (R)	7" (178 mm)	5,000 units
		13" (330 mm)	20,000 units

NOTE

1. For paper tape and reel specification/dimensions, please see the special data sheet "Chip resistors packing".

FUNCTIONAL DESCRIPTION

POWER RATING

RC0603 rated power at 70°C is I/I0 W

RATED VOLTAGE

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V=\sqrt{(P X R)}$$


or max. working voltage whichever is less


Where

V=Continuous rated DC or AC (rms) working voltage (V)

P=Rated power (W)

R=Resistance value (\times)






TESTS AND REQUIREMENTS

Table 4 Test condition, procedure and requirements


TEST METHOD	PROCEDURE	REQUIREMENTS
IEC 60115-1 4.8	At +25/–55 °C and +25/+125 °C	Refer to table 2
	Formula:	
	T.C.R= $\frac{R_2-R_1}{R_1(t_2-t_1)} \times 10^6 \text{ (ppm/°C)}$	
	Where t_1 =+25 °C or specified room temperature	
	t ₂ =-55 °C or +125 °C test temperature	
	R ₁ =resistance at reference temperature in ohms	
	R ₂ =resistance at test temperature in ohms	
IEC 60115-1 4.25.1	1,000 hours at 70±5 °C applied RCWV 1.5 hours on, 0.5 hour off, still air required	$\pm (1.0\% + 0.05 \ \Omega)$ for 0.1%, 0.5%, 1% tol.
		\pm (3.0%+0.05 Ω) for 5% tol.
		$<$ 100 m Ω for Jumper
IEC 60068-2-2	1,000 hours at 155±5 °C, unpowered	\pm (1.0%+0.05 Ω) for 0.1%, 0.5%, 1% tol.
Exposure/ Endurance at Upper Category Temperature		\pm (2.0%+0.05 Ω) for 5% tol.
		$<$ 50 m Ω for Jumper
MIL-STD-202G Method-106G	Each temperature / humidity cycle is defined at 8 hours, 3 cycles / 24 hours for 10d. with 25 °C /	$\pm (0.5\% + 0.05 \ \Omega)$ for 0.1%, 0.5%, 1% tol.
	unpowered	\pm (2.0%+0.05 Ω) for 5% tol.
	Parts mounted on test-boards, without condensation on parts	<100 m Ω for Jumper
	Measurement at 24±2 hours after test conclusion	
MIL-STD-202G Method-107G	-55/+125 °C	±(0.5%+0.05 Ω) for 0.1%,
	Number of cycles required is 300. Devices	0.5%, 1% tol.
	unmounted	\pm (1%+0.05 Ω) for 5% tol.
	Maximum transfer time is 20 seconds. Dwell time is 15 minutes. Air – Air	$<$ 50 m Ω for Jumper
IEC60115-1 4.13	2.5 times of rated voltage or maximum overload voltage whichever is less for 5 sec at room temperature	$\pm (1.0\% + 0.05 \ \Omega)$ for 0.1%, 0.5%, 1% tol.
		$\pm (2.0\% + 0.05 \ \Omega)$ for 5% tol.
		(=, =, 5
		$<$ 50 m Ω for Jumper
	IEC 60115-1 4.8 IEC 60115-1 4.25.1 IEC 60068-2-2 MIL-STD-202G Method-106G	IEC 60115-1 4.8 At +25/-55 °C and +25/+125 °C Formula: T.C.R= R ₂ -R ₁ R ₁ (t ₂ -t ₁) × 10 ⁶ (ppm/°C) Where t ₁ =+25 °C or specified room temperature t ₂ =-55 °C or +125 °C test temperature R ₁ =resistance at reference temperature in ohms R ₂ =resistance at test temperature in ohms R ₂ =resistance at test temperature in ohms IEC 60115-1 4.25.1 I,000 hours at 70±5 °C applied RCWV I.5 hours on, 0.5 hour off, still air required IEC 60068-2-2 I,000 hours at 155±5 °C, unpowered MIL-STD-202G Method-106G Each temperature / humidity cycle is defined at 8 hours, 3 cycles / 24 hours for 10d with 25 °C / 65 °C 95% R.H, without steps 7a & 7b, unpowered Parts mounted on test-boards, without condensation on parts Measurement at 24±2 hours after test conclusion MIL-STD-202G Method-107G -55/+125 °C Number of cycles required is 300. Devices unmounted Maximum transfer time is 20 seconds. Dwell time is 15 minutes. Air – Air IEC60115-1 4.13 2.5 times of rated voltage or maximum overload voltage whichever is less for 5 sec at room





Chip Resistor Surface Mount RC SERIES 0603 (RoHS Compliant)

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Board Flex/ Bending	IEC 60068-2-21	Chips mounted on a 90mm glass epoxy resin PCB (FR4) 3 mm bending Bending time: 60±5 seconds	±(1.0%+0.05 Ω) for 0.1%, 0.5%, 1%, 5% <50 mΩ for Jumper No visible damage
Low Temperature Operation	IEC 60068-2-I	The resistor shall be subjected to a DC rated voltage for 1.5 h-on, 0.5 h-off, at -55±3 °C This constitutes shall be repeated for 96 hours However the applied voltage shall not exceed the maximum operating voltage	±(0.5%+0.05 Ω) for 0.1%, 0.5%, 1% tol. ±(1.0%+0.05 Ω) for 5% tol. No visible damage
Insulation Resistance	IEC 60115-1 4.6	Rated continuous overload voltage (RCOV) for I minute Type RC0603 Voltage (DC) 100 V	≥10 GΩ
Dielectric Withstand Voltage	IEC 60115-1 4.7	Maximum voltage (V _{rms}) applied for 1 minute Type RC0603 Voltage (AC) 100 V _{rms}	No breakdown or flashover
Resistance to Solvent	IPC/JEDEC J-STD-020D	Isopropylalcohol (C3H7OH) followed by brushing	No smeared
Noise	IEC 60115-1 4.12	Maximum voltage (Vrms) applied	Resistors range Value
			$R < 100 \Omega$ 10 dB
			$100 \Omega \le R < 1 K\Omega$ 20 dB
			$I K\Omega \le R < 10 K\Omega$ 30 dB
			$10 \text{ K}\Omega \leq R < 100 \text{ K}\Omega$ 40 dB
			$\frac{100 \text{ K}\Omega \leq \text{R} < \text{I} \text{ M}\Omega}{46 \text{ dB}}$
			$I M\Omega \le R \le 22 M\Omega$ 48 dB
Humidity	IEC 60115-1 4.21	Steady state for 1000 hours at 40 °C / 95% R.H. RCWV applied for 1.5 hours on and 0.5 hour off	\pm (1.0%+0.05 Ω) for 0.1%, 0.5%, 1% tol. \pm (2.0%+0.05 Ω) for 5% tol. <100 mΩ for Jumper



YAGEO Phicomp Chip Resistor Surface Mount RC SERIES 0603 (RoHS Compliant)

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Intermittent Overload	IEC 60115-1 4.39	2.5 times of rated voltage or maximum overload voltage whichever is less for 1 second on and 25 seconds off, total 10,000 cycles	$\pm (1.0\% + 0.05~\Omega)$ for 0.1%, 0.5%, 1% tol. $\pm (2.0\% + 0.05~\Omega)$ for 5% tol. <100 m Ω for Jumper
Solderability - Wetting	IPC/JEDEC J-STD-002B test B	Electrical Test not required Magnification 50X SMD conditions: Ist step: method B, aging 4 hours at 155 °C dry heat 2nd step: leadfree solder bath at 245±3 °C Dipping time: 3±0.5 seconds	Well tinned (≥95% covered) No visible damage
- Leaching	IPC/JEDEC J-STD-002B test D	Leadfree solder, 260 °C, 30 seconds immersion time	No visible damage
- Resistance to Soldering Heat	IEC 60068-2-58	Condition B, no pre-heat of samples Leadfree solder, 260 °C, 10 seconds immersion time Procedure 2 for SMD: devices fluxed and cleaned with isopropanol	\pm (0.5%+0.05 Ω) for 0.1%, 0.5%, 1% tol. \pm (1.0%+0.05 Ω) for 5% tol. <50 mΩ for Jumper No visible damage



REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 5	Jun. 25, 2014		- Add 0.5% tolerance for RC0603
			- update test method
Version 4	Apr. 24, 2009	-	- Test Items and methods updated
			- Test requirements upgraded
Version 3	Jul. 15, 2008	-	- Change to dual brand datasheet that describe RC0603 with RoHS compliant
			- Description of "Halogen Free Epoxy" added
			- Define global part number
Version 2	Aug. 19, 2004	-	
Version I	Aug. 02, 2004	· -	- New datasheet for 0603 thick film 1% and 5% with lead-free terminations
			- Replace the 0603 part of pdf files: RC01_I1_21_31_5, RC02_12_22_32_10, and HRC21_5_4
			- Test method and procedure updated
			- PE tape added (paper tape will be replaced by PE tape)
			- High ohmic products combined into standard products.

[&]quot;Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itself are unchanged. Any product change will be announced by PCN."

